

## Portable Dissolved Oxygen Meter




### 9-in-1 Meter with Lab Performance

Dissolved Oxygen concentration/saturation, pH, mV, Conductivity, TDS, Salinity, Resistivity and Temperature

#### Features:

- Automatic salinity compensation and manual barometric pressure compensation for DO measurements
- Waterproof housing (meets IP57)
- One button pH calibration (4, 7, and 10pH)
- Choice of 3 point pH calibration for better accuracy
- One point Conductivity calibration – automatically recognizes 8 calibration solutions from USA, Europe and China series
- Automatic Temperature Compensation (non-linear compensation for purified water <10µS/cm to improve measuring accuracy)
- Memory stores up to 400 readings with series number, measured value and temperature
- Large blue backlit dual LCD display
- Auto power off saves battery life with disable function
- Complete with Dissolved Oxygen probe with 3 membrane caps and DO internal fill solution (30mL), pH/mV/Temperature electrode, polymer Conductivity cell, pH calibration solutions (4, 7, and 10pH), Conductivity calibration solution (1413µS), 2 AA batteries, and hard carrying case



Read to use complete kit includes all the necessary accessories stored in a hard carrying case for easy transportation. Ideal for field use.

Large blue backlit dual LCD display with calibration and memory indicators

Specifications	
Dissolved Oxygen	Concentration: 0 to 40.00mg/L; Saturation: 0 to 200.0%
pH	-2.00 to 19.99pH
mV	-1999 to + 1999mV
Conductivity	0.00 to 199.9mS
TDS	0 to 100g/L
Salinity	0 to 100ppt
Resistivity	0 to 100MΩcm
Temperature	32 to 212°F (0 to 100°C), pH and mV 32 to 122°F (0 to 50°C), all other ranges
Resolution	0.01m/g/L, 0.1%, 0.01pH, 1mV, 0.01µS, 0.1°
Accuracy	±0.02pH; ±0.15mV; ±1.5%FS; ±1°F/±0.5°C
Power	Two AA batteries
Dimension	Meter: 4.7 x 2.6 x 1.2" (120 x 65 x 31mm) Kit: 14 x 10.75 x 3" (355.6 x 273 x 76.2mm)
Weight	Meter: 6.3oz (180g) Kit: 3.75lbs (1.7kg)

#### Ordering Information:

- DO700.....Waterproof pH/mV/Conductivity/TDS/Salinity/Temp Meter
- DO705.....Dissolved Oxygen Electrode
- DO703.....Replacement Membrane Caps (3 caps)
- PH305.....Spare pH/mV/Temperature Electrode
- EC605.....Spare Polymer Conductivity Cell



**airconcern**

more info for Extech DO700

Phone: 01235 838 555

Email: [cs@airconcern.co.uk](mailto:cs@airconcern.co.uk)

Web: [www.airconcern.co.uk](http://www.airconcern.co.uk)

Air Concern Ltd, Building 173 Curie Avenue Harvell Didcot, Oxfordshire